

LUVOCOM® 3F PAHT KK 50056 BK FR

LUVOCOM® 3F

Additive manufacturing solutions

High-temperature polyamide
with ceramic spheres, flame retardant, black

halogen free

Physical properties		Test method	Specimen	Units	Typical value
Specific gravity		ISO 1183-3		g/cm ³	1,49
Water absorption	23°C / 24h	ISO 62	MPTS ISO 3167 A	%	<0,3
Linear mould shrinkage		DIN 16742	MPTS ISO 3167 A	%	0,0-0,1
Flammability behaviour		UL 94	1/16"		(V-0)
Mechanical properties at 23°C / 50% rh					
Tensile strength	dry, @50 mm/min	ISO 527	MPTS ISO 3167 A	MPa	55
Elongation at maximum force	dry, @50 mm/min	ISO 527	MPTS ISO 3167 A	%	1,2
Modulus of elasticity	dry, @1 mm/min	ISO 527	MPTS ISO 3167 A	GPa	6
Thermal properties					
Heat distortion temperature	HDT A	ISO 75	molded sample	°C	90
Continuous service temperature	20.000 h	IEC 60216	MPTS ISO 3167 A	°C	120
Service temperature	during lifetime max. 200h		MPTS ISO 3167 A	°C	160
Electrical properties					
Insulation resistance strip electrode	R25	DIN IEC 60167	MPTS ISO 3167 A	Ω	>10 ⁹
Surface resistance	ROB	DIN IEC 60093	Ronde 60x4mm	Ω	>10 ⁹

Main features

Easy to print. No warping.

LUVOCOM® 3F PAHT KK 50056 BK FR

LUVOCOM® 3F

Additive manufacturing solutions

High-temperature polyamide
with ceramic spheres, flame retardant, black

halogen free

Recommended processing parameters

General

3D Printing parameters may vary from machine to machine. The following settings may be used as an indication: nozzle temperature: 265 - 290 °C / nozzle material: abbrasion resistant / print bed temperature: > 50 °C / layer thickness: > 0,2mm / printing speed 40 - 60 mm/s.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application. Please contact us for further information.

Predrying

It is advisable to predry the granulate with a suitable dryer immediately before processing. The granulate may absorb moisture from the environment.

Dryer type	Temperature °C	Drying time in h
Dehumidifying dryer	130	6 - 8
Vacuum Dryer	120	4 - 6

Processing

Zone 1	°C	260 - 300
Zone 2	°C	260 - 300
Zone 3	°C	260 - 300
Nozzle	°C	250 - 290
Melt temperature	°C	280

In general LUVOCOM® 3F can be processed on conventional extrusion machines while observing the usual technical guidelines. Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder, screw and die should be protected against wear as is usual in the processing of reinforced thermoplastic materials. Lengthy dwell times for the melts in the cylinder should be avoided. Lower the temperatures during interruptions!

Delivery form & storage

Unless indicated otherwise, the material is delivered as 3mm long pellets in sealed bags on pallets. Preferably storage should be effected in dry and normally temperatured rooms.

Additional information

Filaments produced from this material may be wound into standard size spools.

50056 21 01 20

Europe and Head Office

Lehmann&Voss&Co. KG
 Alsterufer 19
 20354 Hamburg
 Germany
 Tel +49 40 44 197-0
 Email: luvocom@lehvoss.de

North America

LEHVOSS North America, LLC
 185 South Broad Street
 Pawcatuck, CT 06379
 USA
 Tel +1-855-681-3226
 Email: info@ehvoss.us

Asia

LEHVOSS (Shanghai) Chemical Trading Co., Ltd.
 Unit 4805, 8 Xingyi Road
 Changning District, Shanghai 200336
 China
 Tel +86 21 62785181
 Email: info@ehvoss.cn

